




SMARTLAM^{2.0}

The most versatile manual polishing machine

909 M DOSING UNIT



M.M. 909 M dosing unit technical data

Distribution system	Distribution of 3 different liquids
Controls	Touch screen
Pumps	3 peristaltic pumps, with 1 outlet to drive an external pump
Electrical power supply	230 v single-phase 50 Hz
Dosing / machine communication	1 x 24 V input for machine servoing
Option	Replacement of a standard peristaltic pump by a high flow rate pump for high-viscosity products
Reference	08 00799 10

Easy cleaning: spinning function, removable water input, easy tank removal



SMARTLAM^{2.0}

MADE IN FRANCE

The SMARTLAM^{2.0} is a compact, single plate polishing machine that gives you a wide range of possibilities both in manual and semi-automatic polishing. Ergonomic and easy-to-use, the SMARTLAM^{2.0} is entirely controlled by a colour touch screen equipped with an intuitive interface. The internal memory can store 9 programs that can be exported via the USB port.

The power of the bidirectional rotation, variable-speed, constant-torque motor and the possibility to use plates with a diameter from 200 to 300 mm are exclusive assets that will allow you to face up to all situations encountered in metallographic research polishing.

Evolutive

Thanks to the mechanical pressure head option SPRINGLAM[®] and the central-pressure holders but also use of the M.M. 909 M programmable dosing unit slaved to the machine, you will have a very efficient, semi-automatic polishing system.

Options: SPRINGLAM[®] pressure head to use the SMARTLAM[®] as a semi-automatic polisher

Variable pressure thanks to the 0- 250 N spring

Attachment system for central pressure sample-holder

Sample-holder Ø 119 mm 6 alveolus water drops for Ø 20 to 32 mm



Technical data	SMARTLAM ^{2.0}
Plate Capacity	Ø 200 to 300 mm
Body	Steel, coated with epoxy paint
Bowl	Removable resin basin for easy cleaning
Controls	3,5" touch screen to control the machine: start/stop, timer, speed and direction of plate, water solenoid valve
Plate rotation speed	Variable from 20 to 650 rpm
Rotation	Clockwise / counter-clockwise
Programming	Loads 9 programs
Connection	Slave connector for dosing unit
Water inlet	Removable pipe with flow-rate adjustment and safety solenoid valve
Power max	0,75 kW
Voltage	230 V - 50 Hz single-phase
Dimensions W x H x D	450 x 300 x 650 mm
Weight	30 kg
Reference	60 SL200 00